




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PART#	DESCRIPTION	WEIGHT*
CJS6X88TGY	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)

*WEIGHT IS APPROXIMATE

- NOTES:
- B**
1. BLUE TERMINATION CAP DESIGNATES CATEGORY 6A PERFORMANCE.
 2. MATERIAL:
MODULE HOUSING- ABS
SHIELD - TIN PLATED PHOS. BRONZE.
WIRE CAP-PC
 3. ALL CATEGORY 6A, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
 4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.



ACTUAL SIZE

MODEL FILENAME	MO1874AI_10GTX_SHLD_ASSY_03	SIZE	A
DRAWING FILENAME	MO2479NU_DC359/03B		
TITLE	A TX6A 10GIG SHIELDED JACK MODULE CUSTOMER DRAWING		
 PANDUIT TM CORP. TINLEY PARK, ILL 60477	I.I. NUMBER		
	PRODUCT SPEC		
	WORK INSTRUCTION		
	SCALE		FULL
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		
	DRAWN BY AFW		PART NO. CJS6X88TGY
	DATE 3-11-06		DRAWING NO. 02479-359
CHK'D	REVIEW DRAWING NUMBERS		

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	11-26-08	BJN		B. NOTES 1 & 3 NOW CATEGORY 6A A. WAS TX6 10GIG SHIELDED JACK	02479-359				
1	11-07-06	MDJr	NGM	RELEASED TO PRODUCTION	02479-359	TRW	TRW		
R	3-11-06	AFW		ADDED Rohs COMPLIANT P/N.					