




Right Angle
Boardmount
(Thru Clearance Cut)

.050"
9 thru 100 Contacts





MK

MATING MATRIX	
CONNECTOR	MATES WITH
MK-2R...	MK, ML, MM, MN receptacles
MK-2S...	MK, ML, MM, MN plugs

MK-2R2-031-335-220S
(PLUG)



MK-2S2-031-445-220S
(RCPT)



(PLUG SHOWN)

DIMENSIONS																	
SIZE	CONTACT ROWS	A	B		C		D	F	H	J		W	X MAX	Y MAX	Z	HARDWARE	MOUNTING HOLE
			PLUG MAX	RCPT MAX	PLUG MAX	RCPT MAX				PLUG	RCPT						
9	2	.775	.334	.400	.185	.251	.565	.020	.183	.195	.250	.420	.420	.775	#2-56 UNC THD	.096 DIA OR #2-56 UNC THREADED INSERT	
15		.925	.484	.550			.715	.925									
21		1.075	.634	.700			.865	1.075									
25		1.175	.734	.800			.965	1.175									
31		1.325	.884	.950			1.115	1.080									
37		1.475	1.034	1.100			1.265	1.180									
51	3	1.425	.984	1.050	.228	.294	1.215	.150	.341	.300	.430	.650	1.220	#4-40 UNC THD	.125 DIA #2-56 UNC INSERT #4-40 UNC INSERT		
69		1.725	1.284	1.350			1.515					.755	1.450				
100	4	2.160	1.384	1.508	.271	.394	1.800	.200	.384			.400	.590			1.000	1.810