

- NOTES:
1. ALL PARTS TO BE BULK PACKED
 2. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE
 3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS



ASS'Y P/N	GROMMET SIZE
W6282-XPG-P-311	CABLE O.D. .09-.14 [2.3 - 3.6]
W6282-XPG-P-315	CABLE O.D. .15-.17 [3.8 - 4.3]
W6282-XPG-P-318	CABLE O.D. .18-.20 [4.6 - 5.1]
W6282-XPG-P-321	CABLE O.D. .21-.23 [5.3 - 5.8]

ASSEMBLY P / N	CONTACTS
W6282-2PG-P-3XX	2 #20
W6282-3PG-P-3XX	3 #20
W6282-4PG-P-3XX	4 #20
W6282-5PG-P-3XX	5 #20
W6282-6PG-P-3XX	6 #20
W6282-XPG-P-3XX	


GROMMET SIZE FOR
SINGLE GROMMET OR
"DC" FOR DAISY CHAIN

NUMBER OF CONTACTS


DAISY CHAIN GROMMETS
FOR W6282-XPG-P-3DC
.125 I.D. FOR CABLES .09-.14 [2.3 - 3.6] O.D.
.188 I.D. FOR CABLES .18-.20 [4.6 - 5.1] O.D.
.250 I.D. FOR CABLES .24-.26 [6.1 - 6.6] O.D.




WIRING END
W6282-2PG-P-3XX




WIRING END
W6282-3PG-P-3XX



WIRING END
W6282-4PG-P-3XX



WIRING END
W6282-5PG-P-3XX



WIRING END
W6282-6PG-P-3XX

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY: _____	DATE: _____

RoHS COMPLIANT

A	MA	03-02-20	RELEASED PER PDR 16014-7	
	PNK	11-25/19	BACKSHELL P/N 6284 CHANGES TO 6284V4	
	PNK	05-10-19	PDR 16014	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK	DATE: 05-10-19
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±0.010 ANGLES ±1° FRACTIONS ±1/16 ± CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			CHECKED BY:	 601 E. WILDWOOD VILLA PARK, IL 60181
			APPROVED BY:	
			SCALE: NTS SIZE: B SHEET: 1 OF 1	
FILE: W6282-XPG-P-3XX			DIRECTORY: SLW	TITLE: CABLE-END ASSEMBLY 2-6 #20 PIN CONTACTS, SOLDER INSTA-CLICK™ MINI-CON-X
			PART NUMBER: W6282-XPG-P-3XX	CUSTOMER: STANDARD PRODUCT
			REV A	