


Coaxial PCB Connector 81_BMA-50-0-1/111_N

Description

Straight PCB plug

Interface Standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0018 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Related Documents

Outline drawing	DOU-00013034
Catalogue drawing	DCA-00013036

Ordering Information

Single package	81_BMA-50-0-1/111_NE
----------------	----------------------

Remarks

PCB connector without stand-offs