




NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 - A5
5. CONNECTOR IS PART MARKED: 3017W5PAM99A10X CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance			 dim. in mm		scale: 2:1 (5:1)							
															material: SEE NOTES							
															date	name		title: D-SUB COMBINATION MALE 17W5P SOLDER CUP				
															drawn	04.01.2016	Unkrüer					
															appd.	04.01.2016	Lehmenkühler					
															norm							
															d-old			dwg no:			DIN-A3 sh: 1	
										a	Original								13K1A5132			
										rev.	description	date	name	part no: 3017W5PAM99A10X								

RoHS compliant