





LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A4	ADDED NEW DASH NUMBER -9 AND I-0	24SEP2012	CZ	SZ
			A6	ADD NEW DASH NUMBER I-1	15DEC2014	CZ	SZ

- 1 COMPANY TRADEMARK, PART NUMBER, AND DATE CODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2 MATERIAL: THERMO PLASTIC, UL94 V-0.
- 3 DATUM LOCATIONS AND BASIC DIMENSIONS TO BE ESTABLISHED BY THE CUSTOMER.
- 4 BULKHEAD THICKNESS RANGE: .031 - .100.
- 5 CONNECTOR MATED TO PANEL FROM OPPOSITE SIDE.
- 6 NO BURRS ALLOWED ON OPPOSITE (MATING) SIDE.
- 7 CONNECTOR KEEP OUT ZONE.
- 8 MOUNT CONNECTOR WITH TYCO HARDWARE KIT I600914-3 FOR .050 (1.27mm) MIN RADIAL FLOAT.
- 9 VARIABLE DIMENSIONS PLEASE REFER TO BOM TABLE FOR DETAIL.



ISOMETRIC VIEW
SCALE 3:2

.400	1.825	-	-	2.175	3.225	2.735	OP + 60S + OP	I-1600626-1
.425	1.775	.250	.925	2.125	3.175	2.685	OP + 16S + 4P	I-1600626-0
.425	1.675	.250	.825	2.025	3.075	2.585	OP + 12S + 4P	1600626-9
.375	1.600	.250	.750	1.950	3.000	2.510	OP + 12S + 4P	1600626-6
.425	3.700	9	1.175	4.050	5.100	4.610	24S + 3ACP + 7P	1600626-5
.425	2.500	.500	.875	2.850	3.900	3.410	OP + 12S + 4ACP	1600626-4
.425	3.100	.300	.875	3.450	4.500	4.010	OP + 12S + 8ACP	1600626-3
.425	3.200	.300	1.575	3.550	4.600	4.110	OP + 40S + 6ACP	1600626-2
.425	3.475	.250	1.125	3.825	4.875	4.385	OP + 24S + 10P	1600626-1
DIM W	DIM U	DIM T	DIM R	DIM L	DIM F	DIM E	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL: 2

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.01
1 PLC ±.01
2 PLC ±.01
3 PLC ±.005
4 PLC ±.0020
ANGLES ±.2°
FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: D. RINGLER 16SEP2003
CHK: M. CORRELL 18SEP2003
APVD: -

PRODUCT SPEC: 108-2157
APPLICATION SPEC: 114-13112
WEIGHT: -













CUSTOMER DRAWING

NAME: PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL

SIZE: 100779
CAGE CODE: 1600626
DRAWING NO: 1600626

RESTRICTED TO: -

SCALE: 4:1
SHEET: 1 OF 3
REV: A6

PART NUMBER	ROWS		POWER									SIGNAL																																																																																																																																																																																						
			P10	P9	P8	P7	P6	P5	P4	P3	P2	P1	6	5	4	3	2		1																																																																																																																																																																															
1600626-5	D C B A																																																																																																																																																																																																	











REFERENCE WIRE CHART AND CONTACTS		
HOUSING MODULE	CONTACT	INSULATION DIAMETER RANGE
.300 POWER	8-10 1600960 REF	[.176 - .272]
.250 POWER	8-10 1600960 REF	[.176 - .203]
	12-14 1600961 REF	[.156 - .176]
.200 POWER	12-14 1600961 REF	[.120 - .156]
.100 SIGNAL	22 - 26 531216-5 REF	[.036 - .069]



THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG <u>D. RINGER</u>	16SEP2003			TE Connectivity	
						CHEK <u>M. CORRELL</u>	18SEP2003				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:				NAME	PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL				
		0 PLOC ± .01				PRODUCT SPEC	SIZE CASE CODE DRAWING NO RESTRICTED TO				
		2 PLOC ± .01				108-2157					
		3 PLOC ± .005				APPLICATION SPEC					
		4 PLOC ± .0020				114-13112					
ANGLES		FINGER ± .002				WEIGHT	A1 00779C-1600626 -				
MATERIAL		FINISH				CUSTOMER DRAWING SCALE 4:1 SHEET 2 OF 3 REV A6					

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS		POWER				SIGNAL			
			P4	P3	P2	P1	3	2	1	
1600626-9	D						E	E	E	
	C						E	E	E	
	B						E	E	E	
	A						E	E	E	
0P + 12S + 4P										

PART NUMBER	ROWS		POWER				SIGNAL				
			P4	P3	P2	P1	4	3	2	1	
1-1600626-0	D						E	E	E	E	
	E						E	E	E		
	E						E	E	E		
	E						E	E	E		
	E						E	E	E		
0P + 16S + 4P											

PART NUMBER	ROWS		SIGNAL															
			15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
I-1600626-1	D																	
	C		E	E	E	E	E	E	E	E	E	E	E	E	E	E		
	B		E	E	E	E	E	E	E	E	E	E	E	E	E	E		
	A		E	E	E	E	E	E	E	E	E	E	E	E	E	E		
			E	E	E	E	E	E	E	E	E	E	E	E	E	E		
0P + 60S + 0P																		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER	16SEP2003	 TE Connectivity			
		CHK M. CORRELL	18SEP2003				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL	
		0 PLC	±	PRODUCT SPEC 108-2157 APPLICATION SPEC 114-13112	SIZE A1	CAGE CODE 100779	DRAWING NO C=1600626
		1 PLC	±				
		2 PLC	±.01				
		3 PLC	±.005				
		4 PLC	±.0020				
ANGLES		±2°		RESTRICTED TO -			
MATERIAL -	FINISH -	WEIGHT -		SCALE 4:1			
CUSTOMER DRAWING				SHEET 3		OF 3	
				REV A6			