







| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
| △                                              |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |

#### Material:

- Item ① Terminal housing: PBT (UL94V-0)
- Item ② Male contact : Copper. Gold plated.
- Item ③ Contact : Brass ,Tin Plated.
- Item ④ With flange nut: Steel zinc plated.

#### Electrical:

- Voltage rating: 600 V
- Current rating: 115 A
- Withstanding Voltage: 2.2 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

KU 04 C 2 x 1 xxxx G

No. OF POLES  
04: 4 POLES

#### COLOR

- 0: BLACK
- 5: GREEN (RAL 6018/T)
- 6: BLUE
- 8: GREY (RAL 7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by  
customer request.  
please contact sales  
department.

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                                                                                             |                      |                      |              |         |             |            |
|----------|---------------------------------------------------------------------------------------------|----------------------|----------------------|--------------|---------|-------------|------------|
| TITLE    | KU 15.0mm Body Series (Right angle) W/F and shield feed-through on the inside of the device |                      |                      |              |         |             |            |
| PART NO. | KU04C2x1xxxxG                                                                               |                      |                      | DWG NO.      | 8KU0001 |             |            |
| APPROVED | CHECKED                                                                                     | DESIGNED             | DRAWN                | CUST NO.     |         |             |            |
|          |                                                                                             | Runner<br>2011.04.25 | Runner<br>2010.05.24 |              |         | UNIT: mm    | X. ±0.50   |
|          |                                                                                             |                      |                      |              |         | SCALE: NONE | X.X ±0.30  |
|          |                                                                                             |                      |                      | SHEET: 01/01 | REV.: B |             | X.XX ±0.10 |
|          |                                                                                             |                      |                      |              |         |             | X° ±1°     |