

Product data sheet

Characteristics

XACA9411

Push button head, Harmony XAC, plastic, white, booted, spring return



Main

Range of Product	Harmony XAC
Product or Component Type	Head for push-button
Component name	XACA

Complementary

Marking	Unmarked
Operator additional information	Booted
Cap/operator or lens colour	White
Product Compatibility	XACA..
Mounting Location	Front of enclosure
Sale per indivisible quantity	10
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60204-32 UL 508
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Overvoltage category	Class II IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 EN 50102
Net Weight	0.02 lb(US) (0.01 kg)

Ordering and shipping details

Category	22473-PUSHBUTTON, PENDANTS
Discount Schedule	CS2
GTIN	3389110645132
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	0.32 oz (9.0 g)
Unit Type of Package 2	BAG
Number of Units in Package 2	10

Package 2 Height	1.18 in (3.0 cm)
Package 2 Width	4.33 in (11.0 cm)
Package 2 Length	3.94 in (10.0 cm)
Package 2 Weight	3.35 oz (95.0 g)
Unit Type of Package 3	S03
Number of Units in Package 3	700
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	15.67 lb(US) (7.11 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------