




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AJ-156-11	1	HOUSING, JACK CABLE	#303 STAINLESS STEEL
2	AJ-155-30	1	INSERT 5-COND, CRIMP SLEEVE	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER
5	AP-136-8	1	NUT ADAPTER	BRASS, BLACK CHROME
6	AP-136-6	1	CLAMP SHIELD, OUTER	NICKEL PLATED BRASS
7	AP-136-5	1	CLAMP SHIELD, INNER	NICKEL PLATED BRASS
8	SEE TABLE #1	1	BUSHING	RUBBER
9	SEE TABLE #1	1	WASHER	STAINLESS STEEL
10	SEE TABLE #1	1	SPRING	#302 STAINLESS STEEL
11	AP-116-6	1	STUD	ANODIZED ALUMINUM ALLOY

C AJ-155S

TABLE #1				
PART NUMBER	CABLE DIA.	BUSHING	WASHER	SPRING
AJ-155S/11-1	$\varnothing .165 \pm .010$	AP-116-17	AP-116-2	AP-116-4
AJ-155S/11-2	$\varnothing .228 \pm .010$	AP-116-18	AP-116-2	AP-116-4
AJ-155S	$\varnothing .250 \pm .010$	AP-116-8	AP-116-2	AP-116-4
AJ-155S/11-4	$\varnothing .290 \pm .010$	AP-116-19	AP-116-2	AP-116-4
AJ-155S/11-5	$\varnothing .320 \pm .010$	AP-116-20	AP-116-22	AP-116-21

NOTES:
1) MARK PART NUMBER & MANUFACTURERS NAME, LOCATED APPROXIMATELY AS SHOWN.



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

						DWN.BY	HR	DATE	6/10/14	MATERIAL				
						CHECKED BY		DATE		FINISH				
						APPR.BY		DATE		WEIGHT	_____	SCALE = 2.00 :1		
						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES & OR (mm)				TITLE JACK 5-PIN AUDIO, CRIMP SLEEVE				
					TOLERANCES:									
					DECIMAL:									
A	NEW RELEASE	202	6/10 2014	HR	±.XX(X.X) ±.XX(X.X) ±.XX(X.X)			±.XXXX(X.XXX) ±.00(X.0.XX) ±.0000(X.0XX)			SIZE C		DWG. NO. AJ-155S	
LET.	REVISION	CN #	DATE	CHK	FRACTION: ±XXXX ± XXXX			ANGLES: ± X° ± X°						
										DO NOT SCALE DWG.		SHEET 1 OF 1		