









NOTES:

- METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- NO CONTACTS ON POS. A1 + A2
- CONNECTOR IS PART MARKED: 3017W2SAR99A10X CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			 dim. in mm	scale: 2:1 (5:1)				
								material: SEE NOTES				
				DO NOT ALTER CAD DRAWING BY HAND			date		name		title: D-SUB COMBINATION FEMALE 17W2S	
							drawn	08.06.16	Lehmenkühler			
							appd.	09.06.16	Koch			
norm												
			d-old				dwg no: 13K1A5224		DIN-A3 sh: 1			
a		Original										
rev.	description	date	name									