

SUMMARY

Wires



Image is for illustrative purpose only

Series	3W
Termination type	No contacts / Accessory
IP rating	68
AWG wire size	0.00 - 0.00
Cable Ø	0.00 - 0.00 mm
Status	active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	BFG*: Cap for plug (G key)
Keying	1 key (alpha=0; Plug: male contacts; Receptacle: female contacts)
Housing Material	
Weight	56.06 g

Performance

Configuration
Insulator
Rated Current

Specifications

Contact LEMO for performance details.

Others

Endurance (Shell): 1000 mating cycles
Temp (min / max): -20°C / +135°C
Humidity (max): <=95% [at 60 deg C /140 F]
Climatical Category: 20/200/21
Shielding (min): 95 dB (10 MHz)


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Shielding (min): 80 dB (1 GHz)

Salt Spray Corrosion: >144 hr

Pressure: 30 bars

DRAWINGS



Dimensions

	A	B	L	N	S1	e
mm.	27.8	6	22	120	26	M24x1.0
in.	1,09	0,24	0,87	4,72	1,02	

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.