


Specification Sheet

Part Number: 151-02661

Two-sided triple 11mm USCAR connector bank with 11mm slots for mounts provides exceptional versatility for mounting of connectors. Two 11mm USCAR connector slots on opposite side provides options for incorporating connector clips with mounting features.

Each connector clip and connector slot is designed to meet USCAR EWCAP-005-11 clip slot specifications.

Meets installation and extraction requirements of SAE/USCAR-2.



USCAR Connector Clip Bank, (3) 11mm 2-Side Conn Clips w/(2) 11mm Conn Slot, POM, Natural, 2000/ctn

Article Number	151-02661
-----------------------	-----------

Type	TRIPLE11CCBRKT
-------------	----------------

Color	Natural (NA)
--------------	--------------

Quantity Per	carton
---------------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
----------------------------	--

Short Description	USCAR Connector Clip Bank, (3) 11mm 2-Side Conn Clips w/(2) 11mm Conn Slot, POM, Natural, 2000/ctn
--------------------------	--

Global Part Name	TRIPLE11CCBRKT-POM-NA
Length L (Imperial)	2.874
Length L (Metric)	73.0
Width W (Imperial)	1.409
Width W (Metric)	35.8
Height H (Imperial)	0.4
Height H (Metric)	10.2
Material	Polyacetal (POM)
Material Shortcut	POM
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	No
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000

Customs Number

3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)