



THERMOSTAT TECHNICAL DATA	
THERMAL PERFORMANCE	
OPEN TEMP :	106°C +- 4°C
CLOSE TEMP :	MANUAL RESET
TEMP CODE :	L106C
ELECTRICAL PERFORMANCE	
VOLTAGE :	240 VOLTS AC
LOAD :	10 AMPS
CONTACT RESISTANCE :	50 MILLI OHMS MAX
COMPONENT DETAILS	
CAP/BRACKET (B201) :	STAINLESS STEEL
TERMINALS (T147) :	STEEL (NICKEL PLATING)
BASE (3450RCM) :	CERAMIC
CONTACTS :	SILVER PLATING
CODING REQUIREMENTS	
L106C 9082-443 U 3450RCM DATE CODE(e.g. U95G)	



THERMOSTAT 3450RCM-9082-443
2 : 1