


MATERIAL NUMBER	OLD PART NUMBER
1300350081	DNEST



VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	8 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

COMPONENT	MATERIAL	FINISH
INSERT	TPE	YELLOW
CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
OVERMOLD	TPE	RED

RELEASE
EC NO: IPG2014-0577
DRWN: GGUSTAFS 2013/10/21
CH'KD: BARDEN
APPR: BWOODMAN2013/10/31

DESCRIPTION
REV

QUALITY
SYMBOL
=0
=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)
mm INCH
4 PLACES ±--- ±---
3 PLACES ±--- ±.005
2 PLACES ±0.13 ±.010
1 PLACE ±0.25 ±.020
ANGULAR ±.5°
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM
DRAWN BY DATE
GGUSTAFS 2013/10/21
CHECKED BY DATE
BARDEN 2013/11/12
APPROVED BY DATE
BWOODMAN 2013/10/31
MATERIAL NO.
SEE CHART
SIZE C
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE
NTS
DESIGN UNITS
INCH
THIRD ANGLE
PROJECTION
EMERGENCY STOP
& AUX POWER TEE
MOLEX INCORPORATED
DOCUMENT NO.
SD-130035-016
SHEET NO.
1 OF 1

