


DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

LOC		DIST		REVISONS					
G		14		P	F	LTR	DESCRIPTION	DATE	APPROVED
						H	REVISED & REDRAWN PER G-5803	6/12/92	DKS / AJK



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

322254

PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm (IN)
TOLERANCES ON:
2 PLC DEC ± 0.20(0.008)
3 PLC DEC ± -
ANGLES ± -

MATERIAL

COPPER ASTM B-152
ANNEALED

FINISH

TIN PLATE
0.0025(0.000100) MIN
THK PER MIL-T-10727

DR 6/12/92
DK SCHUM

CHK 6/26/92
RD HEIN

APPD 6/26/92
AJ KAUFMAN

APPD 6/26/92
CR RHODS

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, SOLISTRAND™
WIRE SIZE: 127.0-152.0mm² [250-300] MCM

SIZE

A

CAGE CODE

00779

DRAWING NO

C-322254

SCALE

1:1

SHEET

1 OF 1

AMP 1489-32 REV 3-92

12 JUN 1992

10:22:16

AMP26463

<US128A>DEPT1123>DWG1123>U.SOL STRAND>U.MCM

CUSTOMER DRAWING