

Han PushPull PFT metal circular HIFF



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 012 0312
Specification	Han PushPull PFT metal circular HIFF
HARTING eCatalogue	https://b2b.harting.com/09350120312

Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	for circular panel cut out

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61076-3-117 EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	49 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053922
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors