

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19



BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
0		作成 (RELEASED)	FJ00-1109-97	30JUL97	K.F	K.S
A		変更 (REVISED)	FJ00-0858-99	18MAY99	K.F	K.O



注記

△ -Z- 面より8.5mmの位置で測定

2 推奨取付ねじ: JIS B1115, B1122 タップねじ, なべ2種

呼び径3, 長さ6mm以下 (締付けトルク: 0.4N.m (4Kg-cm) 以下)

NOTE

△ MEASURED AT THE SECTION 8.5mm FROM -Z-

2 RECOMMENDED SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW

OF 3DIA X 6LEN(MAX) (JIS B1115, B1122)

(FASTENING TORQUE FOR SCREW: 0.4N.m (4Kg-cm) MAX)

A-A

B-B

① 段ボール	GRAY 灰色	1-353222-6
通箱	GRAY 灰色	353222-6
梱包形態	HOUSING COLOR ハウジング色	P/N
APVD K. SHIMIZU	30JUL97	NAME K. FUCHIBE
CHK K. ODA	30JUL97	30JUL97
PRODUCT SPEC 108-5580(-1)	126極 キャップ ハウジング アッセンブリ .040II/.070II HD ハイブリット I/O コネクタ .040X102極, .070X24極	SIZE A2
INSTRUCTION SHEET 411-5828(-1)	CAGE CODE 00779	DRAWING NO. C-353222
WEIGHT 54.3g	SCALE 1-1	SHEET 1 OF 1
CUSTOMER DRAWING	REV A	