

Between Series Adaptor 33_F-N-75-51/033_-

Description

Adaptor plug/jack
F plug (male) / N jack (female)

Interface standards
Series F - IEC 60169-24
Series N - Not compatible to N 50 Ohms



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	2 GHz

Mechanical Data

Number of matings	500
Weight	0.0374 kg

Environmental Data

Operating temperature	-50 °C to 70 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - F plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	Nickel Plating

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00014357
-----------------	--------------

Ordering Information

Single package	33_F-N-75-51/033_-E
----------------	---------------------