

Coaxial Cable Connector 24_NEX10-50-2-1/033_-

Description

Straight bulkhead cable jack

Interface standards

NEX10

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	20 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00343229
Catalogue drawing	DCA-00345210

Ordering Information

Bulk 100 pcs package	24_NEX10-50-2-1/033_-Y
----------------------	------------------------

Additional Information

Suitable cables	SUCOFORM_86
-----------------	-------------