




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-18-004355	19JUN2018	BDA	SG

- 1 MATERIAL:
HOUSING- NYLON, 4/6, HIGH TEMP, BLACK.
CONTACT- COPPER ALLOY
CAVITY CARRIER TAPE- BLACK CONDUCTIVE PLOYCARBONATE
- 2 FINISH:
CONTACT - TIN PLATE
- 3 POST TO WITHSTAND 13 NEWTONS [3 LBS] MIN AXIAL
FORCE IN THIS DIRECTION WITHOUT DISLODGING, BEFORE
SOLDERING.
- 4 POSTS SOLDERTAILS MUST COMPLY WITH TE SOLDERABILITY
SPEC 109-11-2.
- 5 MEASURED AT -A-
- 6 APPLIES WHEN HEADER IS HELD STRAIGHT
- 7 COORDINATE DIM APPLIES FROM CENTER OF ACTUAL FEATURE.
- 8 DIMENSION APPLY TO THE COMPONENT SIDE OF BOARD
- 9 MAX TEMP EXPOSURE DURING REFLOW SOLDERING MAY NOT
EXCEED 280°C [536°F].
- 10 HEADERS ARE SUPPLIED ON A 330.2mm [13] DIAMETER REEL
WITH 225 PARTS PER REEL. THE CAVITY CARRIER TAPE
HOLDS 1 PART PER POCKET, ORIENTED AS SHOWN.
- 11 TE LOGO, UL AND CSA TRADEMARKS MARKED AT THIS LOACTION






VIEW B-B




1.26 [32MM]	1 REQ'D	1 REQ'D	4	2331450-4
1.26 [32MM]	1 REQ'D	1 REQ'D	3	2331450-3
.945 [24MM]	1 REQ'D	1 REQ'D	2	2331450-2
DIM A	PICK AND PLACE COVER	HEADER ASSEMBLY	NO. OF POSITIONS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 01MAR2018 BASVESH WARAD		 TE Connectivity			
DIMENSIONS: INCHES		CHK 01MAR2018 GUERRIERO, SHAYNIA					
		APVD 01MAR2018 GUERRIERO, SHAYNIA		NAME MTA100 HDR ASSY,SM,FL,SN, HT, T&R			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		—					
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=2331450	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 3:1	SHEET 1 of 3	REV A1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



MTA-100 4P HEADER SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASVESH WARAD 01MAR2018	TE Connectivity		
DIMENSIONS: INCHES		CHK GUERRIERO, SHAYNIA 01MAR2018			
		APVD GUERRIERO, SHAYNIA 01MAR2018	NAME MTA100 HDR ASSY,SM,FL,SN, HT, T&R		
		PRODUCT SPEC	---		
		APPLICATION SPEC	---		
		WEIGHT	---		
MATERIAL ---		FINISH ---	SIZE A2	CAGE CODE 00779	DRAWING NO C-2331450
		CUSTOMER DRAWING		SCALE 5:1	SHEET 2 OF 3
				REV A1	



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



CAP FOR HEADER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN01MAR2018BASVESH WARAD

CHK01MAR2018GUERRIERO, SHAYNIA

APVD01MAR2018GUERRIERO, SHAYNIA

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .015
4 PLC ± -
ANGLES ± 1°

MATERIAL-

FINISH-

WEIGHT-

CUSTOMER DRAWING

01MAR2018

TE Connectivity

NAME

MTA100 HDR ASSY,SM,FL,SN, HT, T&R

SIZEA2

CAGE CODE00779

DRAWING NOC-2331450

RESTRICTED TO-

SCALE10:1

SHEET3 OF 3

REVA1