

Coaxial Cable Connector 24_MMCX-50-2-1/111_O

Description

Straight bulkhead cable feed through

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	soldered
Weight	0.0009 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (without Nickel underplating)
Washer	Bronze	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00009970
Catalogue drawing	DCA-00009291
Assembly instruction	DOC-0000180170
Mounting hole	DOU-00009144

Ordering Information

Single package	24_MMCX-50-2-1/111_OE
----------------	-----------------------

Additional Information

Suitable cables	EZ_86_TP_M17
-----------------	--------------