





HOLDDOWN:BRASS,100u" TIN OVER 50u" NICKEL
SHEEL:SPCC,50u" NICKEL PLATING OVERALL
RIVET:BRASS,NICKEL PLATING OVERALL
SCREWLOCK:BRASS,Ni PLATED

STANDS FOR CALENDAR YEAR
STANDS FOR WEEK NUMBER



3.18 [0.13]	300U BLUE	NO SEE DETAIL Z	30 μ "Au	2311586-5
3.18 [0.13]	300U BLUE	NO SEE DETAIL Z	Au Flash	2311586-4
2.7 [0.11]	BLACK	YES	15 μ "Au	2311586-3
2.7 [0.11]	661C BLUE	YES	Au Flash	2311586-2
3.18 [0.13]	300U BLUE	YES	Au Flash	2311586-1
X $\pm$ 0.38 [$\pm$ 0.015] POST LENGTH	HOUSING COLOR	SCREWLOCK	Contact Area Plating	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 20FEB2017 AJITH PAI CHK 20FEB2017 DANIEL GORENC APVD 20FEB2017 DANIEL GORENC		 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 15P			
		PRODUCT SPEC 108-130023					
		APPLICATION SPEC -					
MATERIAL -		FINISH -		WEIGHT A2 00779			
				DRAWING NO C=2311586			
				RESTRICTED TO -			
CUSTOMER DRAWING				SCALE 3:1			
				SHEET 1 OF 1			
				REV D			