




A

B		A		NO. OF POSN		ASSEMBLY PART NUMBER	
LED DOCUMENT.		DWG. 04AN004 REV. 03V		TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK. J. OLSON APVD J. OLSON PRODUCT SPEC 108-25026 APPLICATION SPEC 114-25018				NAME	
± - ± 0.13 [005] ± - ± -				AMPMODU MOD II RECEPTACLE ASSEMBLY, HORIZONTAL, .100 CL, 2 ROW, CLOSED-ENTRY, SHORT POINT OF CONTACT, END-TO-END STACKABLE			
		SIZE		GAGE CODE		DRAWING NO	
		A1		00779		C-5535512	
WEIGHT		-				RESTRICTED TO	
						-	
3		CUSTOMER DRAWING		SCALE		SHEET	
				5:1		1 of 1	
						REV B	

- | | | | | | | | |
|---|--|--|--|---|--|-------------------------|--|
| B | | A | | NO. OF
POSN | | ASSEMBLY
PART NUMBER | |
| LED DOCUMENT. | | DWG. 04AN004
ESV
CHK -
APVD J OLSON
PRODUCT SPEC
108-25026
APPLICATION SPEC
114-25018 | |  TE Connectivity

AMPMODU MOD II RECEPTACLE ASSEMBLY,
HORIZONTAL, .100 CL, 2 ROW, CLOSED-ENTRY,
SHORT POINT OF CONTACT, END-TO-END STACKABLE | | NAME | |
| TOLERANCES UNLESS
OTHERWISE SPECIFIED:
± -
± 0.13 [005]
± -
± - | | SIZE GAGE CODE DRAWING NO | | | | RESTRICTED TO | |
| WEIGHT - | | A1 00779 | | C-5535512 | | - | |
|  3 | | CUSTOMER DRAWING | | SCALE 5:1 | | SHEET 1 of 1 REV B | |