

General information

Part number	S20LOC-P04PFC0-320S	 <p>Illustrations may differ from original product. Dimensions, unless otherwise specified, in mm.</p>
Termination	crimp	
Size	0	
Locking principle	push	
Coding	0_key	
Cable Diameter	cable_mini_32	
Cable outlet	bend_relief	



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	4
Contact type	pins
Contact diameter	0.7mm
Insulator material	peek
Wire cross section	28-32_awg
Termination	crimp
Data transmission	ethernet_100

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	0.8_mm	10_mm
Nominal current single contact	0.6_a	iec_60512_5_2
Nominal current insert	6_A	vde_0298_4
Test voltage	0.9_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip50
Operating temperature	40_120_c
Mating cycles	5000

mated_unmated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2

data_text

ul_text

illustrative_text