





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECR-18-001902	9FEB2018	JH	PKS



- 1 SPECIFICATIONS:
MAGNET WIRE #27 - #36 AWG, 0.36[.0142] - 0.13[.005] DIA. COPPER
LEAD WIRE #20 AWG,(0.5MM2), STRANDED, BONDED OR SOLID
INSULATED LEAD WIRE. MAX INSULATION O.D. 2.9[.115] NO STRIPPING
REQUIRED. OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2 POCKET RECOMMENDATION : #1601433
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114-13166 FIGURE 3 OR 4.
- 4 TWO(2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.
- 5 PRELIMINARY-NOT FOR PRODUCTION



-	-	-
-	-	-
POST TIN PLATED OVER NICKEL	-	1601237-2 5
UNPLATED	050-021-000	4-1601237-1
UNPLATED	150-022-000	2-1601237-1
UNPLATED	150-021-000	1601237-1
FINISH	REFERENCE PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 27JUN2007		 TE Connectivity Ltd.			
		CHK G JACONO 27JUN2007					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME FINE WIRE RANGE TO 20 AWG. SEMI-RIGID SIAMEZE TERMINAL —			
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± 2°		APVD G JACONO 27JUN2007				
			PRODUCT SPEC 108-2244				
MATERIAL BRASS, SPRING HARD		FINISH SEE TABLE		APPLICATION SPEC — 			
		WEIGHT 0.000000		SIZE A2	CAGE CODE 00779	DRAWING NO C=1601237	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1	REV A2