

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		REVISED PER ECO-16-016715	23NOV2016	RS	MZ

D

C

B




A

D

C

B

A




VIEW B-B

OBSOLETE	6.10 [.240]	$\frac{6}{4}$	213859-4
	6.20 [.244]	$\frac{4}{4}$	213859-3
	15.70 [.618]	$\frac{6}{4}$	213859-2
OBSOLETE	15.70 [.618]	$\frac{4}{4}$	213859-1
	DIM A	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 01-06-95	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.STONE 01-09-95		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	
0 PLC ± -		PRODUCT SPEC	108-10024	
1 PLC ± -		APPLICATION SPEC	114-10038	
2 PLC ± 0.25 [.010]		WEIGHT	-	
3 PLC ± 0.127 [.0050]		SCALE	2:1	
4 PLC ± -		SHEET	1 of 2	
ANGLES ± -		REV	F	
FINISH		CONTACT: SEE TABLE		
MATERIAL: HOUSING:		CUSTOMER DRAWING		
CONTACT SPRING:				
CONTACT BODY & POST:				

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 01-06-95 CHK R.STONE 01-09-95		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± 0.127 [.0050] 4 PLC ± - ANGLES ± ±		NAME RECEPTACLE ASSEMBLY, POSTED, STANDARD SEX, 23-19, CPC	
		APVD - PRODUCT SPEC 108-10024 APPLICATION SPEC 114-10038		SIZE A2	
MATERIAL HOUSING:  CONTACT SPRING:  CONTACT BODY & POST: 		FINISH CONTACT: SEE TABLE		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C=213859	
		CUSTOMER DRAWING		RESTRICTED TO -	
		SCALE 2:1		SHEET 2 of 2	
		REV F			

213859

1

A