



8

0

0

0

0

0

0

1B

68

0.00 - 0.00 mm

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	HM*: Fixed receptacle with grounding tab, nut fixing, watertight or vacuum-tight (back panel mounting)
Keying	
Housing Material	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
Cable Fixing	∅ 0 - 0 mm
Variant	P : Watertight

Performance

Configuration	1B.308 : 8 Low Voltage
Insulator	L: PEEK
Rated Current	5 Amps

Specifications

Contact Type: Special


Others

Temp (min / max): -20° C / +80° C
Humidity (max): <=95% [at 60 deg C / 140 F]
Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]
 Salt Spray Corrosion: >144 hr
 Climatical Category: 20/80/21
 Shielding (min): 75 dB (10 MHz)
 Shielding (min): 40 dB (1 GHz)
 Pressure: 60 bars
 IP Rating: 68

DRAWINGS

Draws



Dimensions

	A	B	E	L	M	P	S1	e
mm.	16	18	5.5	26	3.5	11	10.5	M12x1.0
in.	0.63	0.71	0.22	1.02	0.14	0.43	0.41	

RECOMMENDED BY LEMO

Tools

Positionner: DCE.91.071.BVM
 Spanner: DCH.91.161.PA

Cables

BELDEN 7921A	PVC	Undefined	
LC.700545			
LC.HZC27.2628			
lc.sgg08.2801	Silicone		

