

Han B Protect Cover Die Cast f Hood PG16



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 30 010 5457 |
| Specification | Han B Protect Cover Die Cast f Hood PG16 |
| HARTING eCatalogue | https://b2b.harting.com/09300105457 |

Identification

| | |
|------------------------------|--|
| Category | Accessories |
| Series of hoods/housings | Han [®] B |
| Type of accessory | Protection cover |
| Description of the accessory | for hoods Metal With fixing cord |

Version

| | |
|--------------|------------------------------------|
| Size | 10 B |
| Locking type | Double locking lever (on the hood) |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-----------------------------|---------------|
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|----------------------|
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |
| | Nickel |
| | Naphthalene |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) |
| | R23 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 56 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140045385 |
| ETIM | EC002314 |
| eCl@ss | 27440208 Cap for industrial connectors |