

620-053 Backshell Accessory Thread Strain Reliefs



62

620-053 M 16 A


Basic Part No. _____

Finish (Table II) _____



Clamp Style _____

Dash No. _____



STYLE A
Medium Duty
(Table V)




STYLE B
Medium Duty
(Table III)




STYLE C
Medium Duty
(Table III)




STYLE D
Medium Duty
(Table V)



STYLE E
Medium Duty
(Table III)



STYLE H
Heavy Duty
(Table IV)



STYLE M
Medium Duty
(Table V)




TABLE III: CABLE ENTRY

Dash No.	D Max		E Max		F Max		G Ref		H Max		J Max		K - Cable Range	
													Min *	Max
03	1.031	(26.2)	1.375	(34.9)	.812	(20.6)	.135	(3.4)	.781	(19.8)	.812	(20.6)	.156 (4.0)	.219 (5.6)
04	1.031	(26.2)	1.375	(34.9)	.937	(23.8)	.203	(5.2)	.781	(19.8)	.937	(23.8)	.188 (4.8)	.312 (7.9)
06	1.031	(26.2)	1.375	(34.9)	1.062	(27.0)	.285	(7.2)	.781	(19.8)	1.062	(27.0)	.281 (7.1)	.438 (11.1)
08	1.031	(26.2)	1.375	(34.9)	1.188	(30.2)	.350	(8.9)	.781	(19.8)	1.188	(30.2)	.312 (7.9)	.531 (13.5)
10	1.094	(27.8)	1.437	(36.5)	1.312	(33.3)	.390	(9.9)	.844	(21.4)	1.312	(33.3)	.375 (9.5)	.625 (15.9)
12	1.219	(31.0)	1.437	(36.5)	1.562	(39.7)	.460	(11.7)	.875	(22.2)	1.562	(39.7)	.500 (12.7)	.750 (19.1)
16	1.219	(31.0)	1.562	(39.7)	1.750	(44.5)	.510	(13.0)	.875	(22.2)	1.750	(44.5)	.625 (15.9)	.938 (23.8)
20	1.344	(34.1)	1.812	(46.0)	2.250	(57.2)	.695	(17.7)	.969	(24.6)	2.250	(57.2)	.938 (23.8)	1.250 (31.8)
24	1.547	(39.3)	2.062	(52.4)	2.375	(60.3)	.715	(18.2)	1.188	(30.2)	2.375	(60.3)	1.000 (25.4)	1.375 (34.9)
28	1.547	(39.3)	2.062	(52.4)	2.625	(66.7)	.915	(23.2)	1.188	(30.2)	2.625	(66.7)	1.250 (31.8)	1.625 (41.3)
32	1.734	(44.0)	2.188	(55.6)	2.812	(71.4)	1.070	(27.2)	1.375	(34.9)	2.812	(71.4)	1.500 (38.1)	1.875 (47.6)

* Not Applicable Styles B and E

TABLE IV: CABLE ENTRY

Dash No.	L Max		M Max		N - Cable Range	
					Min	Max
04	1.312	(33.3)	.957	(24.3)	.125 (3.2)	.312 (7.9)
06	1.312	(33.3)	1.145	(29.1)	.250 (6.4)	.437 (11.1)
08	1.312	(33.3)	1.332	(33.8)	.312 (7.9)	.562 (14.3)
10	1.312	(33.3)	1.332	(33.8)	.350 (8.9)	.625 (15.9)
12	1.344	(34.1)	1.551	(39.4)	.500 (12.7)	.750 (19.1)
16	1.438	(36.5)	1.770	(45.0)	.625 (15.9)	.937 (23.8)
20	1.625	(41.3)	2.113	(53.7)	.875 (22.2)	1.250 (31.8)
24	1.688	(42.9)	2.363	(60.0)	1.000 (25.4)	1.375 (34.9)
28	1.938	(49.2)	2.770	(70.4)	1.250 (31.8)	1.625 (41.3)
32	1.938	(49.2)	3.020	(76.7)	1.437 (36.5)	1.875 (47.6)

See inside back cover fold-out or page 14 for Table II.

1. Metric dimensions (mm) are indicated in parentheses.
2. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
3. Style C saddles are bottomed on clamp ears.

TABLE V: CABLE ENTRY

Dash No.	P Max		R Max		S Max		T Max		W Max		X - Cable Range	
											Min **	Max
03*	.844	(21.4)	n/a		.562	(14.3)	.843	(21.4)	.630	(16.0)	.156 (4.0)	.250 (6.4)
04*	.844	(21.4)	n/a		.562	(14.3)	.906	(23.0)	.755	(19.2)	.188 (4.8)	.312 (7.9)
06*	.906	(23.0)	n/a		.562	(14.3)	1.093	(27.8)	.942	(23.9)	.281 (7.1)	.438 (11.1)
08	.969	(24.6)	1.312	(33.3)	.562	(14.3)	1.187	(30.1)	1.067	(27.1)	.344 (8.7)	.562 (14.3)
10	.969	(24.6)	1.312	(33.3)	.562	(14.3)	1.281	(32.5)	1.192	(30.3)	.375 (9.5)	.625 (15.9)
12	.969	(24.6)	1.344	(34.1)	.562	(14.3)	1.500	(38.1)	1.380	(35.1)	.438 (11.1)	.750 (19.1)
16	1.062	(27.0)	1.688	(42.9)	.562	(14.3)	1.719	(43.7)	1.535	(39.0)	.562 (14.3)	.938 (23.8)
20	1.125	(28.6)	1.906	(48.4)	.562	(14.3)	2.062	(52.4)	1.848	(46.9)	.750 (19.1)	1.250 (31.8)
24	1.188	(30.2)	1.906	(48.4)	.594	(15.1)	2.312	(58.7)	2.255	(57.3)	.781 (19.8)	1.375 (34.9)
28	1.719	(43.7)	2.125	(54.0)	.594	(15.1)	2.719	(69.1)	2.505	(63.6)	.969 (24.6)	1.625 (41.3)
32*	1.781	(45.2)	n/a		.750	(19.1)	2.969	(75.4)	2.755	(70.0)	1.125 (28.6)	1.875 (47.6)
40*	1.781	(45.2)	n/a		.812	(20.6)	3.531	(89.7)	3.255	(82.7)	1.469 (37.3)	2.375 (60.3)

* Not available in Style M clamp.

** Not Applicable Style D