



SIZE	A DIA	B DIA	T THREAD	JACKSCREW P/N	RET RING P/N
1.0mm	ø.060	ø.0655	1.00UNM (0.25mm PITCH)	1589283-3	1589284-1
1.2mm	ø.065	ø.0735	1.20UNM (0.25mm PITCH)	1589283-4	1589284-2



STANDARD JACKSCREW 



STANDARD RETAINING RING $\triangle_2 \triangle_3$

- 1 JACKSCREW MATERIAL: 303 STAINLESS STEEL PER ASTM A581, CONDITION A, PASSIVATE PER SAE-AMS-2700, TYPE 2, DRY FILM LUBE PER DOD-L-85645 TYPE I
- 2 RETAINING RING MATERIAL: 17-4 STAINLESS STEEL PER ASTM A564, CONDITION A, PASSIVATE PER SAE-AMS-2700, TYPE 2
- 3 DIMENSIONS FOR RETAINING RING ARE PRIOR TO INSTALLATION ONTO THE JACKSCREW. RETAINING RING MUST BE CRIMPED AROUND THE SHAFT OF THE SCREW TO PROPERLY CAPTIVATE THE SCREW ONTO DUALOBE PLUG CONNECTORS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M STORY 17 DEC 02		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK —			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD M STORY 1 DEC 10		STANDARD NANONICS JACKSCREW AND RETAINING RING, 1.0mm AND 1.2mm SIZES	
		PRODUCT SPEC —		—	
		APPLICATION SPEC —		—	
MATERIAL		FINISH		SIZE	CAGE CODE
SEE NOTES		SEE NOTES		DRAWING NO	
		WEIGHT —		RESTRICTED TO	
		A2		0PJN9	
		C=303-0076		—	
		CUSTOMER DRAWING		SCALE	SHEET
				24:1	1 of 1
				REV	F