



Minimum cable diameter: 3
 Maximum cable diameter:
 - with rubber bushing: 8
 - without rubber bushing: 8,5
 - without reduction plate: 12,5

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4
				Detail.	27/06/08 PK	
				Insp.		
				Stand.		
EC00368	07/07/09	PK	HARTING EURL			TB 09 67 025 032X Sub.
35063	27/06/08	PK	F-95972 Paris			
Mod.	Dot.	Name				

D-Sub, 25 poles, top entry, straight metal hood with threaded inserts, for cable to cable application with latching		Maßstab/ Scale
		1,5:1
Blatt/ Page		1 / 1

09 67 025 0323	M3
09 67 025 0322	4-40 UNC
Part number	Threaded insert