




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	ECO-21-006943	13OCT2021	RK	MZ



1. THIS CONNECTOR WILL ACCEPT TWO TYPE I, SIZE 12 SOCKET CONTACTS AND EIGHT MULTIMATE SOCKET CONTACTS.
 2. TYPE I CONTACTS MATE FIRST, BREAK LAST.
 3. MAX WIRE INSULATION USED WITH THIS RECEPTACLE IS 2.67[.105] DIA FOR MULTIMATE SOCKET CONTACTS.
- 4 TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 05/23/95	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 5-25-95				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.FRANTUM 5-25-95	NAME		
	0 PLC ± -		PRODUCT SPEC	RECEPTACLE, ARR 17-10M, REVERSE SEX, SERIES 4, CLASS A, FREE-HANGING, CPC		
	1 PLC ± -		APPLICATION SPEC			
	2 PLC ± 0.25 [.010]					
MATERIAL NYLON, BLACK		FINISH -	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-213129
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV F	RESTRICTED TO -