

5

4

3

2

1

D

C

B

A

cable clamp

cable clamp screw

shell screw

cable ϕ_6^8

Hood cap

Hood

Holding caps

Ruber gasket

O-ring seal

Holding frame

detail A

15.6 $\pm 0,3$

12.4 $\pm 0,3$

41 $\pm 0,3$

25,0 $\pm 0,3$

17,0 $\pm 0,3$

15,60 $\pm 0,3$

25 $\pm 0,1$

33.6 $\pm 0,3$

Mounting instructions

The stripped braid should not be fold back to avoid damaging the cable clamp and reducing its performance

23 $\pm 0,30$

5 $\pm 0,30$

3,50 $\begin{smallmatrix} 0 \\ -0,50 \end{smallmatrix}$

	Dat.	Name
Detail.	07/01/04	S.H.
Insp.		
Stand.		



All Dim. in mm
Orig. Size DIN A 4

D-SUB IP67 9 Poles
BLACK plastic hood

Moßstab/
Scale

1/1

31587

07/01/04

S.H.

HARTING ELEKTRONIK
F-95972 Paris



TB 09 67 009 0436

Sub.

Blatt/ Page