



Datasheet for part number DCMD-37S-J-F225

Our Catalog Part Number: DCMD-37S-J-F225	
Brand: Cannon	Product Category: D Sub Product Line: D Sub Series: D*M

Product Datasheet	
General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	200
Contact Arrangement	37 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	Passivated stainless steel
Shell Finish	Stainless steel shell
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Socket
Contact Type	Right angled PCB
Contact Material	copper alloy
Contact Finish	gold over nickel
Hardware	90° Metal Bracket, 4-40 Fastener and 4-40 Screwlock
Disclaimer	Our facility is not currently certified by the DLA and this product is not covered by the QPL/QML.