

4

3







2

1

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	00		A	REVISED FB00-0217-04	16DEC04	H.H	I.E

PANEL CUT DIMENSIONS



- NOTES
- MATERIAL
HOUSING:THERMO PLASTIC (BLACK)
CONTACT:COPPER ALLOY
 - CONTACT FINISH
MATING SIDE:NICKEL PL.ALL OVER GOLD PL.
CT MATING SIDE:NICKEL PL.ALL OVER MATTE TIN PL.
 - APPLIED AC CONTACT P/N
- | FINISH | AWG | P/N |
|---------|--------|------------|
| TIN PL. | #16~20 | 1-179321-2 |
| Au PL. | #16~20 | 179321-3 |
- AC: POWER CONTACT (UNLOADED)
DC:SIGNAL CONTACT (PRELOADED)

MT TYPE:173977-5 CLIMPT TYPE:179228-5	4-292190-2	2.5 #0.1	10	13.5	49.3	2	47.3	54.5	17.9	8	21	4	3	DC5 AC4	3-292187-2
MT TYPE:173977-5 CLIMPT TYPE:179228-5	2-292190-2	1.2 #0.08	34	15 MAX	42.3	3.3	40.3	47.5	14.4	8	14	4	2	DC5 AC3	1-292187-2
APPLIED CT CONN P/N	MATING COUNTER P/N	APPLIED PANEL THICKNESS H	K	J	G	F	E	D	C	B	A	n	N	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL SEE NOTE	FINISH SEE NOTE

DWN J.JIANG 05FEB03	CHK S.YAO 05FEB03	APVD T.SASAKI 05FEB03
PRODUCT SPEC 108-60023		
APPLICATION SPEC		
WEIGHT		
CUSTOMER DRAWING		

tyco
Electronics

Tyco Electronics Corporation
Shanghai, P.R.China,200233

NAME
HYBRID SF DRAWER CONN.
PLUG

SIZE A3	CAGE CODE 00779	DRAWING NO C-292187	RESTRICTED TO —
------------	--------------------	------------------------	--------------------

SCALE 2:1	SHEET 1 OF 1	REV A
--------------	-----------------	----------