

Sales Outline Drawing**Revision D**

May not be suitable for all medical and aerospace applications.
Specifications: Contact Mallory Sonalert to discuss your application.

Oscillation Frequency (Hz)	Multiple
Operating Voltage (Vac)	60 ~ 130
Rated Voltage (Vac)	120
Current Consumption (mA)	20 at Rated Voltage
Sound Pressure (dB)	90 @ 1Ft @ Rated Voltage
Tone/Pulse Rate	Fast Chirp
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Lead Pin	Tin Plated Brass
Housing	ABS 757 Plastic resin (Color: Black)
Weight (Grams)	24
Options	For other options contact factory

Dimensions: (units: mm)**ROHS Compliant**