

NOTES: UNLESS OTHERWISE SPECIFIED
 1. MATERIAL SPECIFICATIONS:
 BODY: BERYLLIUM COPPER
 CONTACT: PHOSPHOR BRONZE
 INSULATOR: PTFE
 SPRING: STEEL
 GASKET: SI-RUBBER
 FERRULE: COPPER
 ALL OTHER METAL PARTS: BRASS


2. FINISH SPECIFICATIONS:
 CONTACT: GOLD
 ALL OTHER METAL PARTS: NICKEL

3. ELECTRICAL SPECIFICATIONS:
 IMPEDANCE: 75 OHMS
 FREQUENCY RANGE: DC - 12 GHz
 RETURN LOSS: -30 dB MAX TO 3 GHz
 -20 dB MAX TO 6 GHz




4. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.

5. CRIMP CONTACT TO .042[1.06] SQ AND FERRULE TO .213[5.41] HEX.

5. CONTACT AND FERRULE SHIPPED LOOSE.



RECOMMENDED CABLE STRIPPING DIM'S



CATALOG P/N: HHD360IM

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] .XXX [XXX] ± .005 [0.13] .XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 4:1				KINGS by WINCHESTER Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				HDBNC CRIMP PLUG FOR 360IM CABLE OR EQUIVALENT (RoHS COMPLIANT)			
DRAWN J	DATE 04/21/2015	APPROVED MAR	DATE 04/21/2016				
APPROVED XXX	DATE XX/XX/XX	APPROVED XXX	DATE XX/XX/XX				
A				SDHHD360IM	SHT 1	OF 1	REV A