



LOC	DIST	REVISIONS			
		P	LTB	DESCRIPTION	DATE
ES	00	A		RELEASED	17DEC2009
		AI		ECR-10-007032	31MAR2010





2050723-1 AS SHOWN





SECTION A-A
SCALE 4:1

NOTES

- 1 LEVER ASSEMBLED IN PRE-LOCKED POSITION. LEVER MUST BE LOCKED BEHIND THE DIMPLE.
- 2 PACKAGING: LOOSE PIECE IN BOX.
- 3 TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-120



1 2



1-2050723-4	964826-1	PBT-GF20	VIOLET	4006	A,C,E,I,I	LEVER	1	2
	1-2050724-4	PBT-GF20	GREY	7036		COVER	1	1
1-2050723-3	964826-1	PBT-GF20	VIOLET	4006	D,B,E,I,I	LEVER	1	2
	1-2050724-3	PBT-GF20	BLACK	9011		COVER	1	1
2050723-5	964826-1	PBT-GF20	VIOLET	4006	A,B,E	LEVER	1	2
	2050724-5	PBT-GF20	BROWN	1011		COVER	1	1
2050723-4	964826-1	PBT-GF20	VIOLET	4006	A,C,E	LEVER	1	2
	2050724-4	PBT-GF20	GREY	7036		COVER	1	1
2050723-3	964826-1	PBT-GF20	VIOLET	4006	D,B,E	LEVER	1	2
	2050724-3	PBT-GF20	BLACK	9011		COVER	1	1
2050723-2	964826-1	PBT-GF20	VIOLET	4006	C,D	LEVER	1	2
	2050724-2	PBT-GF20	BLUE	5012		COVER	1	1
2050723-1	964826-1	PBT-GF20	VIOLET	4006	A,F	LEVER	1	2
	2050724-1	PBT-GF20	GREEN	6018		COVER	1	1
TE-ASSY-NO	TE-PART NO	MATERIAL	COLOUR	RAV	CODING	DESCRIPTION	QTY.	ITEM NO

THIS DRAWING IS UNPUBLISHED COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.				DWN J. CHEN 17DEC2009	Tyco Electronics Shanghai, CHINA			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 3				CHK A. GUANCO 17DEC2009	NAME COVER, ASSY, MOS-HSG., 2x16 POS.			
DIMENSIONS mm				APVD K. QDA 17DEC2009	SIZE CAGE CODE DRAWING NO.			
MATERIAL				PRODUCT SPEC 108-18924	RESTRICTED			
SEE TABLE				APPLICATION SPEC 114-18630	A200779C=2050723			
CUSTOMER DRAWING				WEIGHT	SCALE			