















* ASTERISK DENOTES MOMENTARY POSITION

CAT. LISTING		"A"	"B"	"D"	"E"
64AT34-1A					
64AT34-1B					
64AT34-1D					
64AT34-1E					
64AT34-1F					
64AT34-1G					
64AT34-1H					
64AT34-1J					
64AT34-1K					
64AT34-1L					
64AT34-1M					
64AT34-1N					
64AT34-1P	FAA-PMA				
64AT34-3D					
64AT34-3F					
64AT34-3G					
64AT34-5E					
64AT34-5F					
64AT34-5K					
64AT34-5L					
64AT34-5M					
64AT34-5N					
64AT34-7E					
64AT34-7L					
64AT34-7N					
64AT34-514B					
64AT34-514E					
64AT34-514G					
64AT34-514L					
64AT34-514N					
64AT34-514P					



- 1 - UNIT INCLUDES "23SX" TYPE (GOLD CONTACT) BASIC SWITCH (4)
(MEETS REQUIREMENTS OF MIL-PRF-8805)
- 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3 - PLATED TERMINALS WILL ACCEPT "AMP INC" .058 DIA PIN RECEPTACLES
- 4 - SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
- 5 - TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
- 6 - DULL FINISH ON LEVER AND BUSHING
- 7 - FLAT WHITE RESILIENT SILICONE (50 DUROMETER APPROX)
- 8 - SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING (SEE
CHART FOR RECOMMENDED LOCKING COMBINATIONS)
- 9 - FOR REPLACEMENT BUTTON SEE MICRO SWITCH CAT. LIST. 15PA90-6W
- 10 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET
15PA313-AT PER MIL-PRF -8805
- 11 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT
- 12 - FOR MANUFACTURING DETAIL SEE THE CORRESPONDING ASSEMBLY DRAWING
FOR EACH LISTING FOR FAA-PMA.

CHARACTERISTICS	ELECTRICAL DATA
PULLOUT FORCE --- 3 LB MIN-5 LB MAX	CONTACT ARRANGEMENT S P D T (4)
	30 VOLTS DC RATING INDUCTIVE ---SEA LEVEL--- 1/2 AMP 50,000 FT --- 1/2 AMP RESISTIVE ---SEA LEVEL--- 1 AMP 50,000 FT --- 1 AMP MAXIMUM INRUSH ----- 2 AMP

NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	

THIRD ANGLE PROJECTION



DRAWN	SLB	21JUN82
CHECK	CEB	28JUN82
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell

D	TITLE	ASSEMBLY - TOGGLE SWITCH

SIZE C	TYPE I	DRAWING NAME 64AT34 SERIES CHART 2	REV 8
SCALE FULL	WEIGHT 09 LB EST	SHEET 1 OF 1	