

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECR-21-108382	25JUN	RR	SZ

NOTES:

1. MATERIAL:

1.1 HOUSING & INSERT HOUSING: LCP, WITH 30% G.F,
UL94 V-0; COLOR: BLACK

1.2 CONTACT: PHOSPHOR BRONZE.

1.3 SHELL: BRASS.

1.4 MYLAR: SILICONE POLYMER.




2. FINISH:

2.1 CONTACT: (SEE TABLE) GOLD PLATED ON CONTACT AREA.
GOLD FLASH ON SOLDER TAIL.


1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.

2.2 SHELL: 0.508um [20u"] MIN. NICKEL PLATED.

3. WAVE SOLDER CAPABLE TO 265°C PER TE SPEC. 109-202, CONDITION B.

LOGO &
DATE CODE

RECOMMENDED PCB LAYOUT (COMPONENT SIDE)
TOLERANCE: ±0.05
PCB THICKNESS: 1.6mm



	1.27um [50u"]	1734579-4
OBSOLETE	0.762um [30u"]	1734579-3
OBSOLETE	0.381um [15u"]	1734579-2
OBSOLETE	0.152um [6u"]	1734579-1
	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3° FINISH
MATERIAL SEE NOTE	SEE NOTE

DWN B. HSING	270CT2006
CHK S. CHIEN	270CT2006
APVD W. KODAMA	270CT2006
PRODUCT SPEC 108-57527	
APPLICATION SPEC -	
WEIGHT -	

NAME MODULAR JACK CONNECTOR RJ45, 8P8C SHIELDED, TAB DOWN, DIP TYPE			
SIZE A3	CAGE CODE 00779	DRAWING NO C-1734579	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 5
		REV D1	

