


D

C

B

A

A



1. THIS RECEPTACLE WILL MATE WITH ANY 104 POSN.,SIZE 6 PLUG IN AMPLIMITE SERIES.
2. MAXIMUM WIRE INSULATION TO BE USED WITH THIS RECEPTACLE IS .054 DIA.
3. SST RETENTION CLIPS ARE INCLUDED IN INSERTS.

- 4 PACKAGE STAMPED M24308/2-492F & AMP P/N 211541-1
5 PACKAGE STAMPED M24308/2-352F & AMP P/N 211541-2
6 PACKAGE STAMPED M24308/2-363F & AMP P/N 211541-3
7 AMP P/N 204351-1; MIL P/N 57-354, INCLUDED IN KIT
8 AMP P/N 91067-1; MIL P/N M81969/1-04
9 CONNECTOR SUPPLIED WITHOUT CONTACTS; SHOWN FOR ILLUSTRATION ONLY.
10 UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL

SUPSD BY 204546-2 & 91067-1		SAME AS -1 EXCEPT: 6 7 8		211541-3
		SAME AS -1 EXCEPT: 5 7		211541-2
		AS SHOWN 4 9		211541-1
DESCRIPTION				PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.ERDMAN CHK R.GRZYBOWSKI APVD L.ROPIER	7/17/85 9-20-85 9-20-85	 TE Connectivity RECEPTACLE ASS'Y,AMPLIMITE, 104 POSN., SIZE 6, SERIES 90, W/DUAL FLOAT. BUSHING
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± -.005 4 PLC ± - ± 0°30'	APPLICATION SPEC	SIZE	
MATERIAL SEE CALLOUT	FINISH SEE CALLOUT	WEIGHT 0.000000	CAGE CODE A1 00779	
CUSTOMER DRAWING		DRAWING NO 211541		RESTRICTED TO -
SCALE NTS		SHEET 1		OF 1
				REV G