







ITEM #	PART #	QTY	DESCRIPTION
1	TJS-102-1	1	SHELL HALF, RIBBED
2	TJS-102-3	1	JACK ASSEMBLY
3	NX304BB1B	1	SWITCH MOMENTARY (3-TNO)
4	TP-102-20	1	CRIMP, SLEEVE ($\varnothing$.39 X .20)
5	TJS-102-2	1	SHELL, HALF - SMOOTH
6	TJ-106-13	2	#4 WASHER, LOCK
7	TJ-106-14	2	NUT, #4-40 SPECIAL
8	TJS-102-15	2	SCREW



RECOMMENDED CABLE:
WM085/U (5-COND)
FOR USE WITH U-94A/U



NOTES:
1) CRIMPING TOOLS USE M22520/S-01 HAND TOOL W/CRIMP
DIE M22520/5-29, M22520/5-3S OR M22520/5-5S
2) MATING CONNECTORS M9177/1-1, & M9177/2-1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

						DWN.BY HR	DATE Mar-24-14	MATERIAL									
						CHECKED BY	DATE	FINISH									
						APPR.BY	DATE	WEIGHT		SCALE = 1.00 :1		NEXUS STAMFORD,CONN					
						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES & OR [mm]		TITLE									
						TOLERANCES:		CONNECTOR AUDIO				SIZE		DWG. NO.			
						DECIMAL:		AIRBORNE JACK W/SWITCH									
A	NEW RELEASE		198	3/24 2014	HR	FRACTION: ±XXX ± X/XX		ANGLES: ±X ° ± X °		4 CONTACT				C		TJS-102NC	
LET.	REVISION	CN #	DATE	CHK					DO NOT SCALE DWG.		SHEET 1 OF 1						