


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECO-17-002903	20MAR2017	AP	DG



- 1
- RCPT ACCEPTS SIZE 20 DF SOCKET CONTACTS. CONTACTS MUST BE PURCHASED SEPARATELY.
- 2
- ALL PARTS SHIPPED UNASSEMBLED.
- 3
- FLAME RETARDANT 94V-0 RATED, STYRENE POLYOLEFIN OR PVC, BLACK.
- 4
- INSERT - FLAME RETARDANT 94V-0 RATED GLASS FILLED, NYLON OR POLYESTER, BLACK.
- 5
- SHELLS & SHIELDS - STEEL PER ASTM A109.
- 6
- SHELLS & SHIELDS - .000200 MIN TIN PLATE OVER .000100 MIN COPPER UNDERPLATE.
- 7
- COMPONENTS INDIVIDUALLY BULK PACKED.
- 8
- CARBON STEEL, C1022.
- 9
- BLACK ZINC FLAKE COATING.

7	W/ LOGOS	1658658-1
PACKAGING	REMARKS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.REITZEL	31JUL03	TE TE Connectivity		
		CHK	S.BOLASH	31JUL03			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	M.WALMSLEY	31JUL03	NAME
mm		0 PLC ± -		PRODUCT SPEC		108-40030	BULK KIT, RCPT, SHIELDING ENCLOSURE, SIZE 3, 25 POSN, AMPLIMITE HDP-20
		1 PLC ± -		APPLICATION SPEC		114-40030	
MATERIAL		2 PLC ± -		WEIGHT		0.000000	SIZE
		3 PLC ± .020		CUSTOMER DRAWING			CAGE CODE
		4 PLC ± -		SCALE		2:1	DRAWING NO
		ANGLES ± -		SHEET		1 of 1	REV
		FINISH		REV		D	