





RECOMMENDED P.C.B. LAYOUT



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
DN	NONE	DN
2-3	OPEN	2-1

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 28VDC; 2A @250VAC.
5. 2002/95/EC (ROHS) COMPLIANT



D	15526	DIMS FROM 1.02, 1.91	11/11/05	PH
C	15483	ADD RDHS NOTE	11/1/05	PH
B	11341	CHANGED PART DESCRIPTION	3/27/01	CB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

E-SWITCH®				
TITLE				
100 SP-1 T6 B11 M3 Q E				
SCALE	DATE	DR	DWG	REV
2:1	3/27/01	CB	T110010	D