



For more information regarding these connectors, please consult us.

CONNECTORS WITH FLAT GASKET

R141
↓
BNC 50 Ω

R142
↓
BNC 75 Ω

P/N	Description	captive center contact
R141 007 000	straight plug clamp type for 5/50/S+D cable	NO
R141 011 000	straight plug clamp type for 6/75/S cable	NO
R141 015 000	straight plug clamp type for 6/75/S cable	NO
R141 154 000	right angle plug clamp type for 2.6/50/S+D cable	YES
R141 206 000	straight jack clamp type for 5/50/S+D cable	NO
R141 209 000	straight jack clamp type for 6/75/S cable	NO
R141 256 000	straight square flange jack clamp type for 5/50/S+D cable	NO
R141 257 000	straight square flange jack clamp type for 5/50/S cable	NO
R141 261 000	straight square flange jack clamp type for 6/75/S cable	NO
R141 264 000	straight insulated square flange jack clamp type for 6/75/S cable	NO
R142 017 000	straight plug clamp type for 8/75/S+D cable	YES

50 Ω CONNECTORS FOR 75 Ω or 93 Ω CABLE

75 Ω Cable

P/N	Description	captive center contact
R141 004 000	straight plug clamp type for 2,6/75/S cable	YES
R141 011 000	straight plug clamp type for 6/75/S cable	NO
R141 013 000	straight plug clamp type for 6/75/S cable	NO
R141 014 000	straight plug clamp type for 6/75/S cable	YES
R141 015 000	straight plug clamp type for 6/75/S cable	NO
R141 074 000	straight plug clamp type for 6/75/S cable	YES
R141 082 280	straight plug crimp type for PH18 cable	YES
R141 154 000	right angle plug clamp type for 2,6/75/D cable	YES
R141 157 000	right angle plug clamp type for 6/75/S cable	YES
R141 184 000	right angle plug crimp type for 6/75/S cable	YES
R141 209 000	straight jack clamp type for 6/75/S cable	NO
R141 210 000	straight jack clamp type for 6/75/S cable	YES
R141 254 000	straight square flange jack clamp type for 2,6/75/S cable	YES
R141 261 000	straight square flange jack clamp type for 6/75/S cable	NO
R141 264 000	straight insulated square flange jack clamp type for 6/75/S cable	NO
R141 277 000	straight insulated square flange jack clamp type for 2,6/75/S cable	YES
R141 278 000	straight square flange jack clamp type for 2,6/75/S cable	YES
R141 329 000	straight bulkhead jack clamp type for 6/75/S cable	YES
R141 334 161	straight bulkhead jack crimp type for 6/75/S cable	YES
R141 334 500	straight bulkhead jack crimp type for 6/75/S cable	YES

93 Ω Cable

P/N	Description	captive center contact
R141 013 000	straight plug clamp type for 6/93/S cable	NO
R141 014 000	straight plug clamp type for 6/93/S cable	YES
R141 077 000	straight plug crimp type for 3,8/93/S cable	YES