

ROHS Compliant







MAPX	MODIFICATION	DATE	DRAW	APPROVE

General tolerances(mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

0.1/10

±2°



PCB LAYOUT

4	Pin Header	Copper Alloy	Sn Plated
3	Spring	Stainless steel	/
2	Screw	Steel	M2.6/Zn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd

UNLESS OTHERWISE
SPECIFIED TOLERANCES



TITLE:
CUSTOMER DRAWING

DECIMALS:

ANGLES:

PAR	DGL500-NP26V-MG461
DWN	
CHKD	
APVD	
SCALE N:A	UNIT:MM
SIZE:A4	SHEET:1F1
CUSTOMER COPY	REV:A