

TE P/N	TE CD	Nanonics P/N	Part Description
1589066-1	1589066	STG02511378PCN	Dualobe, 2 row, gold, 25 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-2	1589066	STG03711378PCN	Dualobe, 2 row, gold, 37 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-3	1589066	STL00911378PC	Dualobe, 2 row, LCP, 9 position, special 11378 duckbill, plug
1589066-4	1589066	STL00911378PCN	Dualobe, 2 row, LCP, 9 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-5	1589066	STL01511378PCN	Dualobe, 2 row, LCP, 15 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-6	1589066	STL02511378PCN	Dualobe, 2 row, LCP, 25 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-7	1589066	STL03711378PCN	Dualobe, 2 row, LCP, 37 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-8	1589066	STL05111378PCN	Dualobe, 2 row, LCP, 51 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1589066-9	1589066	STL06511378PC	Dualobe, 2 row, LCP, 65 position, special 11378 duckbill, plug.
1-1589066-0	1589066	STL06511378PCN	Dualobe, 2 row, LCP, 65 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1-1589066-1	1589066	STM00911378PCN	Dualobe, 2 row, metal, 9 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1-1589066-2	1589066	STM02511378PC	Dualobe, 2 row, metal, 25 position, special 11378 duckbill, plug.
1-1589066-3	1589066	STM02511378PCN	Dualobe, 2 row, metal, 25 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1-1589066-4	1589066	STM03711378PCN	Dualobe, 2 row, metal, 37 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1-1589066-5	1589066	STM03711378PCQ	Dualobe, 2 row, metal, 37 position, special 11378 duckbill, plug, 1.2 captive jackscrews.
1-1589066-6	1589066	STM05111378PC	Dualobe, 2 row, metal, 51 position, special 11378 duckbill, plug.
1-1589066-7	1589066	STM05111378PCM	Dualobe, 2 row, metal, 65 position, special 11378 duckbill, plug, 1.0 non-captive jackscrews.
1-1589066-8	1589066	STM05111378PCN	Dualobe, 2 row, metal, 51 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
1-1589066-9	1589066	STM05111378PCQ	Dualobe, 2 row, metal, 51 position, special 11378 duckbill, plug, 1.2 captive jackscrews.
2-1589066-0	1589066	STM06511378PCN	Dualobe, 2 row, metal, 65 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
2-1589066-1	1589066	STM06511378PCQ	Dualobe, 2 row, metal, 65 position, special 11378 duckbill, plug, 1.2 captive jackscrews.
2-1589066-2	1589066	STM06511378PC	Dualobe, 2 row, metal, 65 position, special 11378 duckbill, plug.
2-1589066-3	1589066	STM01511378PCN	Dualobe, 2 row, metal, 15 position, special 11378 duckbill, plug, 1.0 captive jackscrews.
2-1589066-4	1589066	STL03711378PC	Dualobe, 2 row, LCP, 37 position, special 11378 duckbill, plug.
2-1589066-5	1589066	STM02511378PCQ	Dualobe, 2 row, metal, 25 position, special 11378 duckbill, plug, 1.2 captive jackscrews.
2-1589066-6	1589066	STM00911378PCQ	Dualobe, 2 row, metal, 9 position, special 11378 duckbill, plug, 1.2 captive jackscrews.
2-1589066-7	1589066	STM01511378PCQ	Dualobe, 2 row, metal, 15 position, special 11378 duckbill, plug, 1.2 captive jackscrews.
2-1589066-8	1589066	STL02511378PC	Dualobe, 2 row, LCP, 25 position, special 11378 duckbill, plug.