







| ▲ SWITCH FUNCTION |        |          |
|-------------------|--------|----------|
| POS. 1            | POS. 2 | POS. 3   |
|                   |        |          |
| ON                | OFF    | ON       |
| 1-2; 4-5          | OFF    | 2-3; 5-6 |



RECOMMENDED  
PANEL CUT-OUT



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A @ 6-30VDC 50/60 Hz,  $\mu$ T85/55  
UL LISTED
5. ELECTRICAL LIFE: 10,000 CYCLES
6. MECHANICAL LIFE: 30,000 CYCLES
7. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
8. DIELECTRIC STRENGTH: >1,500V AC 1MIN
9. INSULATION RESISTANCE: >100 MOHMS @ 500VDC
10. OPERATING TEMP: 0°C to 55°C
11. LED VOLTAGE: 12VDC
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



E-SWITCH®

TITLE R723FB4-SXXX2B4AAW

|     |        |             |         |     |
|-----|--------|-------------|---------|-----|
| A   | 21363  | NEW RELEASE | 1/29/14 | EBP |
| REV | PCR NO | DESCRIPTION | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |                   |           |                |          |
|-------|-------------------|-----------|----------------|----------|
| SCALE | DATE<br>1/29/2014 | DR<br>EBP | DWG<br>C700021 | REV<br>A |
|-------|-------------------|-----------|----------------|----------|