




| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| FT  | 0    |           | D1  | REVISED PER ECO-11-004917 | 11MAR11 | RK  | HMR  |

MATERIAL:  
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.  
TERMINALS: BRIGHT TIN OVER COPPER ALLOY.  
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE. (EXCEPT WHERE NOTED)


ELECTRICAL:  
RATED CURRENT UL/CSA:  
CLASS C: 20A, 300V  
CLASS D: 5A, 600V  
WIRE RANGE: 12-22 AWG

MECHANICAL:  
RECOMMENDED TORQUE: 7 IN-LB  
OPERATING TEMP.: 105°C MAX.

- △2 SCREWS ARE BRASS.
- △3 .250 X .032 QC TABS.
- △4 SCREWS ARE STAINLESS STEEL.
- △5 PRELIMINARY PART NUMBER.



9-796985-8



SEE FIGURE

|    |               |             |                  |             |
|----|---------------|-------------|------------------|-------------|
| △2 | 9.436         | 25          | JC6-P105-25      | 1776346-1   |
|    | 9.436         | 25          | JC6-P107-25      | 8-796985-7  |
|    | 9.061         | 24          | JC6-P107-24      | 8-796985-6  |
|    | 8.686         | 23          | JC6-P107-23      | 8-796985-5  |
|    | 8.311         | 22          | JC6-P107-22      | 8-796985-4  |
|    | 7.936         | 21          | JC6-P107-21      | 8-796985-3  |
|    | 7.561         | 20          | JC6-P107-20      | 5-1437666-5 |
|    | 7.186         | 19          | JC6-P107-19      | 8-796985-2  |
|    | 6.811         | 18          | JC6-P107-18      | 8-796985-1  |
|    | 6.436         | 17          | JC6-P107-17      | 8-796985-0  |
|    | 6.061         | 16          | JC6-P107-16-502  | 9-796985-8  |
|    | 6.061         | 16          | JC6-P107-16      | 1-1437665-9 |
|    | 5.686         | 15          | JC6-P107-15      | 7-796985-9  |
|    | 5.311         | 14          | JC6-P107-14      | 1-1437665-8 |
|    | 4.936         | 13          | JC6-P107-13      | 1-1437665-7 |
| △2 | 4.561         | 12          | JC6-P105-12-165  | 3-796985-9  |
| △2 | 4.561         | 12          | JC6-P105-12      | 3-796985-8  |
|    | 4.561         | 12          | JC6-P107-12      | 1-1437665-6 |
| △5 | 4.186         | 11          | JC6-P107-11-241  | 1776346-7   |
|    | 4.186         | 11          | JC6-P107-11      | 1-1437665-5 |
|    | 3.811         | 10          | JC6-P107-10      | 1-1437665-4 |
| △5 | 3.436         | 9           | JC6-P107-09-240  | 1776346-6   |
|    | 3.436         | 9           | JC6-P107-09      | 1-1437665-3 |
| △5 | 3.061         | 8           | JC6-P107-08-239  | 1776346-5   |
|    | 3.061         | 8           | JC6-P107-08      | 1-1437665-2 |
|    | 2.686         | 7           | JC6-P107-07      | 1-1437665-1 |
| △4 | 2.311         | 6           | JC6-P107-06-220  | 1776346-2   |
| △3 | 2.311         | 6           | JC6-P107-06-166  | 1-796985-1  |
|    | 2.311         | 6           | JC6-P107-06      | 1-1437665-0 |
| △5 | 1.936         | 5           | JC6-P107-05-238  | 1776346-4   |
|    | 1.936         | 5           | JC6-P107-05      | 1437665-9   |
|    | 1.561         | 4           | JC6-P107-04      | 1437665-7   |
|    | 1.186         | 3           | JC6-P107-03      | 1437665-6   |
|    | .811          | 2           | JC6-P107-02      | 1437665-5   |
|    | DIM. "A" REF. | NO. OF POS. | CATALOG PART NO. | PART NO.    |

|                                        |  |                        |                      |                 |                        |                 |
|----------------------------------------|--|------------------------|----------------------|-----------------|------------------------|-----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN S. SCHLEGEL 5/7/03 | TE Connectivity      |                 |                        |                 |
|                                        |  | CHK S. YODER 5/7/03    |                      |                 |                        |                 |
|                                        |  | APVD S. YODER 5/7/03   | NAME                 |                 |                        |                 |
|                                        |  | PRODUCT SPEC           | JC6-P107-XX ASSEMBLY |                 |                        |                 |
|                                        |  | APPLICATION SPEC       |                      |                 |                        |                 |
|                                        |  | WEIGHT -               | SIZE A3              | CAGE CODE 00779 | DRAWING NO C-1437665-5 | RESTRICTED TO - |
| CUSTOMER DRAWING                       |  | SCALE NTS              | SHEET 1 OF 1         | REV D1          |                        |                 |