


BACKSHELL KIT INCLUDES:

- (1) BACKSHELL
- (2) 4-40 THUMBSCREWS
- (1) PLASTIC STRAIN RELIEF
- (1) METAL STRAIN RELIEF CLAMP
- (2) STRAIN RELIEF SCREWS

TORQUE VALUE ON PLASTIC FOR STRAIN RELIEF SCREWS = 4 INCH POUNDS MAX.



972-009-01SRYY1

SERIES _____
POSITIONS _____
009
MATERIAL _____
01S = PLASTIC/SLIM LINE
COLOR: _____
01 = BLACK
03 = LIGHT GREY
04 = GREEN
06 = RED
07 = BLUE
08 = YELLOW
11 = DEC GREY
PUT-UPS _____
1 = KIT

****SEE PAGE 2 FOR
PANTONE COLOR CODES**

	A	B	C	D	E	F
(TOL.) INCHES	± 0.032	± 0.012	± 0.020	± 0.020	± 0.020	
MM	± 0.80	± 0.30	± 0.50	± 0.50	± 0.50	
INCHES	1.240	.984	1.339	.591	1.858	.315
MM	31.50	24.99	34.00	15.00	47.20	8.00

MATERIAL: POLYAMIDE PA66 - UL 94H-B
MANY COLORS AVAILABLE (SEE SHEET 2)
THUMBSCREWS: STEEL, BLACK OXIDE (FOR BLACK HOODS)
STEEL, ZINC PLATED (FOR COLORED HOODS)

OPERATING TEMP: -55°C TO +110°C

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

CHECKED:

DATE:
07-06-15

DATE:

SCALE:

SHEET 1 OF 2

REV 0

NorComp

DWG NO. 972-009-01SRYY1

COLOR RANGE		
COLOR	UPPER	LOWER
01 = BLACK	PANTONE BLACK 3C	PANTONE BLACK 3C
03 = LIGHT GREY	427C	427C
04 = GREEN	7731C	7732C
06 = RED	186C	187C
07 = BLUE	2190C	2191C
08 = YELLOW	108C	109C
11 = DEC GREY	7527C	7534C

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: M. SIGMON		DATE: 07-06-15	
		CHECKED:		DATE:	
		SCALE:	SHEET 2	OF 2	REV 0
NorComp		DWG NO. 972-009-01SRYY1			